

Tel:26280661 Fax: 24902700 Email: project@kashingehk.com Website: www.kashingehk.com



PROJECT	REF	REV	ITEM CODE	
LOCATION	DATE		PAGE	

SANITARY WARE SPECIFICATION SHEET

Item Descriptions Mediclinics "Speedflow® Plus" (Spain)

Stainless Steel AISI 304 inside cabinet automatic hand dryer in satin finish

Dimensions L290 x W100 x H270 mm

Model M17ACS

Material/ Finish Stainless Steel / Satin Finish

Manufacturer Mediclinics, S.A. (Spain)

Source Ka Shing Enterprises (H.K) Limted

Mr. Ivan Lau / Mr. GilmanYuen

Contact Tel/Fax (852) 2628-0661 / (852) 2490-2700

E-mail project@kashingehk.com Website www.kashingehk.com

General description

*The Speedflow® line of hand dryers is categorized within the eco fast range of product but with the added value of complying with the requirements of ADAAG for accessibility of public washrooms. This regulation requires that the depth of the dryer cannot exceed 100 mm to facilitate access and movement of handicapped persons about the *washroom.

*Warm air hand dryer.

*Sensor operated.

*Maximum power and airflow.

*Maximum robustness and vandal-proff.

*Suitable for very high traffic facilities.

*Complies with ADA requirements for a barrier-free washroom.

Components &materials:

*M17A: Steel, finish White epoxy.

*M17AC: AISI 304, stainless steel, finish bright. *M17ACS: AISI 304, stainless steel, finish satin.

*M17AB: Steel, finish black epoxy.

*Aluminum base plate, with 4 holes Ø 7 mm for wall mounting. It includes silent-blocks to damp mechanical vibrations.

*Fire resistant plastic UL 94-V0 fan scroll.



M17A White epoxy finish



M17AB Matte black epoxy finish



M17AC Bright finish




M17ACS Satin finish

Illustration/ Drawing







Technical Specifications

220- 240 V		
50/60 Hz		
Clase I		
675-850 W		
180-350 W		
2.8-5 A (230 V)		
350 W		
23,000 – 32,000		
0 ó 500 W (switch "ON/OFF"		
270x290x100 mm		
3.2 Kg		
1.5 mm		
10 – 12 sec.		
290-400 Km/h		
42 °C		
57-65 dBA		
IP23		

Note:











M17A/M17A-I White finish



M17AB/M17AB-I Black finish



M17AC/M17AC-I Bright finish



M17ACS/M17ACS-I Satin finish


		HAND DRYER CODES		
Cover material	Cover finish	Without Ionizer	With Ionizer	
Steel	White	M17A	M17A-I	
Steel	Black	M17AB	M17AB-I	
Stainless Steel	Bright	M17AC	M17AC-I	
Stainless Steel	Satin	M17ACS	M17ACS-I	


OPERATION


Place the hands under the air outlet. The dryer will automatically start the drying cycle and continue without interruption as long as the hands remain in the sensor actuating area. The appliance will stop working 2 seconds after the hands are removed from the air circulation or after 30 seconds of continuous use of the appliance.

MOUNTING

RECOMMENDED HEIGHTS DISTANCE FROM THE FLOOR







Certificates and Qualifications









