

SANITARY WARE SPECIFICATION SHEET

Model: 511906C

Descriptions: Delabie (France) "Be-Line" Ø35 x 600mm long Matte black power-coated aluminium grab rail

Dimensions: 35mm dia x 600 mm long
Manufacturer: Delabie (France)

Material : Metallised aluminium
Finish : Matte black



ADVANTAGES



Innovative design suitable for all users




Comfort: ergonomic anti-rotation surface



Tested to over 200kg



38mm gap between bar and wall: space saving



* All information of the above is for the reference only. No prior notice is made if any changes.



Ka Shing Enterprise (H.K.) Ltd.

ROOM 1706 NEW TERRITORIES TSUEN WAN HO LIK CENTRE, 66A SHA TSUI ROAD
Tel: 26280661 Fax: 24902700
Email: project@kashinghk.com
Website: www.kashinghk.com

Ivan / Horace 26280661

E/ project@kashinghk.com

W/ <https://www.kashinghk.com/>

DESCRIPTION

Be-Line® anthracite straight grab bar Ø 35mm, L. 600mm

Ref. 511906C

Be-Line® grab bar Ø 35mm, for people with reduced mobility.

For use as a handrail or grab bar for WCs, showers or baths.

Aluminium tube, 3mm thick. Solid aluminium fixing points.

Rounded profile Ø 35mm with ergonomic flat front face that prevents rotation for an optimal grip.

Metallised anthracite powder-coated finish provides a good visual contrast with the wall.

Uniform surface for easy maintenance and hygiene.

38mm gap between the bar and the wall: minimal space prevents the forearm passing between the bar and the wall, reducing the risk of fracture in case of loss of balance.

Concealed fixings.

Supplied with stainless steel screws Ø 8 x 70mm for concrete walls.

600mm centre-to-centre.

Tested to over 200kg. Maximum recommended user weight: 135kg.

INSTALLATION & CARE

EN

- Ensure screws and rawl plugs are suitable for wall mounting and reinforce if necessary.
- Installation should be undertaken by professional installers only.
- Maximum user weight: 135kg. Make sure that the wall and/or surface can support this weight. Reinforce the wall if necessary and/or adapt the surface if necessary.
- Clean using a soft, damp cloth or with cleaning products and disinfectants. Do not use acid-based products or scouring powder.



Product conforms to European standard EN 12182 and the Directive 93/42/CEE.



DELABIE

** All information of the above is for the reference only. No prior notice is made if any changes.*







Ka Shing Enterprise (H.K.) Ltd.

ROOM 1706 NEW TERRITORIES TSUEN WAN HO LIK CENTRE, 66A SHA TSUI ROAD
Tel: 26280661 Fax: 24902700
Email: project@kashingehk.com
Website: www.kashingehk.com

Ivan / Horace 26280661

E/ project@kashingehk.com

W/ [https://www.kashingehk.com/](http://www.kashingehk.com/)



Ka Shing Enterprise (H.K.) Ltd.

ROOM 1706 NEW TERRITORIES TSUEN WAN HO LIK CENTRE, 66A SHA TSUI ROAD
 Tel:26280661 Fax: 24902700
 Email: project@kashingehk.com
 Website: www.kashingehk.com

Ivan / Horace 26280661

E/ project@kashingehk.com

W/ <https://www.kashingehk.com/>